

WE 1010

1-Channel Power Unit, digital, 70 W
Product no.: T0053298699



Benefits

- › Power unit, 1 channel with soldering iron WEP 70 and safety rest PH 70
- › 70W solder iron with ergonomic handle and providing toolless tip change
- › ESD safe station, iron and heat-resistant silicon cable for safe handling
- › Using ET soldering tips
- › Standby mode and auto setback conserves energy, protects equipment
- › Password-protected to preserve settings
- › Replacement for 4ETH, 4ETK, 4ETO, 4ETS necessary. For WEP 70 4ETHL, 4ETKL, 4EKOL and 4ETSL must be used.
- › Change hot tips out by hand by twisting the plastic knurled nut on the soldering pencil without an additional tool.


For this purpose, we recommend:



Solder fume extractors



Soldering irons



Cleaning



Pre-heating plates



Technical Data

| | |
|--|---|
| Dimensions L x W x H (mm) | 150 x 120 x 98 |
| Dimensions L x W x H (inches) | 5.91 x 4.72 x 3.86 |
| Weight (approx.) in kg | 1.4 |
| Voltage | 230 V |
| Power | 85 W |
| Channels | 1 |
| Temperature range (depends on tool) °C | 100 - 450 |
| Temperature range (depends on tool) °F | 200 - 850 |
| Temperature accuracy °C | Average tip temperature can be „offset“ to +/- 5°C at idle with no load |
| Temperature accuracy °F | Average tip temperature can be „offset“ to +/- 9°F at idle with no load |
| Temperature stability °C | ± 6 |
| Temperature stability °F | ± 10 |
| Equipotential bonding socket | --- |
| Display | Digital LC Display |
| Air consumption l/min | --- |
| Operating pressure in bar/psi | --- |
| Capacity l/min | --- |
| Vacuum | --- |

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE