



- Preheating plates
- 1000 W, 230 V
- Heating surface 220 x 150 mm
- Temperature range 50°C - 300°C
- RS 232 Interface e.g. for connection to Weller hot air stations WHA 3000
- Digital display for set and read temperature
- Element Type K (accessory) connectable

WHP 1000 Preheating plate

Product no.: T0053364899N

Dimensions L x W x H (mm)	254 x 280 x 70
Dimensions L x W x H (inches)	10 x 11 x 2.76
Weight (approx.) in kg	---
Voltage	230 V
Power	1000 W
Channels	---
Temperature range (depends on tool) °C	---
Temperature range (depends on tool) °F	---
Temperature accuracy °C	---
Temperature accuracy °F	---
Temperature accuracy for hot air °C	---
Temperature accuracy for hot air °F	---
Temperature stability °C	---
Temperature stability °F	---
Equipotential bonding socket	---
Display	---
Additional vacuum pump	---
Max. hot air flow rate l/min (depends on tool)	---
Capacity l/min	---
Max. vacuum	---
Interface	1 x RS232, 1 x thermocouple type K