



- Infrared preheating plate
- 200 W, 230 V
- Heating surface 120 x 60 mm
- Temperature range 50 °C - 400 °C
- Digital display for set and read temperature
- Electronic temperature control
- Infrared high temperature ceramic elements for fast and efficient heat up
- 2 Easy Fix board holder

### WHP 200 Infrared preheating plate

Product no.: T0053371699N

Dimensions L x W x H (mm)	165 x 195 x 70 mm
Dimensions L x W x H (inches)	6.5 x 7.68 x 2.76 Inch
Weight (approx.) in kg	---
Voltage	220 - 240 V, 50/60 Hz
Power	200 W
Channels	---
Temperature range (depends on tool) °C	---
Temperature range (depends on tool) °F	---
Temperature accuracy °C	---
Temperature accuracy °F	---
Temperature accuracy for hot air °C	---
Temperature accuracy for hot air °F	---
Temperature stability °C	---
Temperature stability °F	---
Equipotential bonding socket	---
Display	---
Additional vacuum pump	---
Max. hot air flow rate l/min (depends on tool)	---
Capacity l/min	---
Max. vacuum	---
Interface	---