



## Main

Range of product	Harmony XAR
Product or component type	Hand-held remote control
Device short name	ZART
Control button type	6 configurable motion push-button 2 configurable auxiliary push-button

## Complementary

Material	Protective cover : EPDM rubber Push-button cover : polyurethane Enclosure : ABS + PC
Display type	5 LEDs
Operating distance	50 m
Communication network type	Wireless : Zigbee
Transmission frequency	2.4 GHz
Maximum sensing distance	100 m in free field
Response time	< 500 ms at simplex
Charging time	10800 s 0 s
Autonomy	150 h with Li-Ion (Lithium-Ion) batteries 100 h
Battery type	Rechargeable 3 x AAA/LR3 alkaline
Mechanical durability	1000000 cycles
Width	85 mm
Height	193 mm
Depth	43 mm
Product weight	0.3 kg

## Environment

Radio agreement	FCC IC
IP degree of protection	IP65
Ambient air temperature for operation	-20...55 °C

---

Ambient air temperature for storage	-20...45 °C
Operating altitude	0...2000 m
Storage altitude	0...3000 m
Relative humidity	0...95 % (temperature : -20...60 °C) (operating)
Product certifications	CE

---

## Offer Sustainability

---

RoHS (date code: YYWW) Compliant - since 0844 - Schneider Electric declaration of conformity  
[!\[\]\(3dfb8d66e81160ad61421a3452093d1b\_img.jpg\) Schneider Electric declaration of conformity](#)

---

## Dimensions

