




Main

Range of product	Harmony XB4 Harmony XB5
Product or component type	Contact block
Device short name	ZBE
Sale per indivisible quantity	1
IP degree of protection	IP20 IEC 60529
Contacts type and composition	1 NO + 1 NC
Contact operation	Slow-break
Contact block type	Double
Contacts usage	High power switching contacts
Connections - terminals	Faston connector 1 x 6.35 mm Faston connector 2 x 2.8 mm

Complementary

Product weight	0.032 kg
Positive opening	With
Mechanical durability	10000000 cycles
Short-circuit protection	10 A cartridge fuse gG EN/IEC 60947-5-1
[I _{th}] conventional free air thermal current	10 A EN/IEC 60947-5-1
[U _i] rated insulation voltage	300 V EN 60947-1
[U _{imp}] rated impulse withstand voltage	6 kV EN 60947-1
[I _e] rated operational current	1.1 A 125 V DC-13 P300 EN/IEC 60947-5-1
Mounting of block	Front mounting
Condition of use	Mounting on push-button collar
Electrical composition code	C15 1
Compatibility code	ZBE

Environment

Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-40...70 °C
Vibration resistance	5 gn 2...500 Hz IEC 60068-2-6

Shock resistance	30 gn 18 ms half sine wave acceleration IEC 60068-2-27
	50 gn 11 ms half sine wave acceleration IEC 60068-2-27

Contractual warranty

Warranty period	18 months
-----------------	-----------