

MAX235H155S orange

- Waterproof and dustproof IP67 certified
- Mil Specs (STANAG 4280, DEF STAN 81-41)
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins, corrosion free

Body and handle: polypropylene copolymer
Latches: nylon
Pins: nylon + 30% fiberglass
O-ring: polymer

COLOURS: black, orange

EXTERNAL DIMENSIONS: 258 x 243 x H167.5 mm (10.16 x 9.56 x H6.59 inch)

INTERNAL DIMENSIONS: 235 x 180 x H156 mm (9.25 x 7.08 x H6.14 inch)

LID-BOTTOM DEPTH: 25 + 131 mm (0.98 + 5.16 inch)

WEIGHT WITH FOAM: 1.06 Kg – 2.34 lbs.

CAPACITY: 10kg – 22 lbs.

CARTON DIMENSIONS: 535 x 260 x 365mm – 21.06 x 10.24 x 14.37 inch

PCS PER CARTON: 4

WEIGHT OF THE CARTON WITH FOAM: 4.92kg – 10.93 lbs.

MOULDING: injection molded

RANGE TEMPERATURE: -30 / 90°C (-22 / 194°F)

FEATURES: IP67, DEF STAN 81-41, STANAG 4280

CUSTOMIZATION: personalized nameplate/resin label

ACCESSORIES: cubed foams

