

## PCB hybrid header - PCH 6/ 4+4-GL4-7,62 BK - 1098839

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid  
(<http://phoenixcontact.com/download>)



PCB hybrid header, nominal current: 41 A, number of positions: 8, pitch: 7.62 mm, color: black, contact surface: Tin, mounting: Wave soldering

Figure shows a 4+4-pos. version with locking flange at position 4

### Your advantages

- ✓ Combining signals and power in a single header saves time and space
- ✓ Easy PCB replacement thanks to plug-in modules
- ✓ Well-known mounting principle allows worldwide use



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
Custom tariff number	85366930
Country of origin	China

### Technical data

Product type	PCB hybrid header
Plug-in system	POWER COMBICON 6 Hybrid
Product family	PCH 6/..+4-GL
Contact type	Male connector
Color	black (9005)
Contact surface material	Tin

## PCB hybrid header - PCH 6/ 4+4-GL4-7,62 BK - 1098839

### Classifications

#### eCl@ss

eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

#### ETIM

ETIM 6.0	EC002637
----------	----------

### Accessories

#### Accessories

#### Coding element

Coding profile - CP-PC RD - 1701967



Coding profile, for plugging into the coding ribs of the plug at a later date, insulating material, color: Red