

Technical Data

Part Number: X4C2000B-W

Product Group: CCTV

Product Type: IP Bullet Camera



Xvision 2MP H265+ Bullet IP Camera, 3.6mm, 40m IR, Starlight

Model: X4C2000B-W	
Style	Bullet Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	No
Mounting Type	Wall or Ceiling
Sensor	1/2.7" Megapixel CMOS Sensor
On Board Camera Functions	Automatic White Balance, Automatic Gain Control, Automatic Electronic Iris, DNR, Starlight, Backlight Compensation, Privacy
Resolution	1080P
Lens Type	Fixed
Lens Size	3.6mm
Viewing Angle	87°

Technical Data

Night Vision	40m IR
Minimum Illumination	0.1 Lux
Video Compression	H265
Video Streams	Dual Stream
Video Resolution & Frame Rates	1920x1080 - 25fps 1280x960 - 25fps 1280x720 - 25fps
Video Bitrate	256Kbps - 8Mbps
Network Connection	RJ45 Socket (10/100)
Network Protocols Supported	TCP/IP, HTTP, DHCP, DNS, DDNS, RTP/RTSP, PPPoE, SMTP, NTP, UPnP, SNMP, HTTPS, FTP
Onvif	Yes
Power Over Ethernet (PoE)	Yes
Power Consumption	<7W
Audio Input	Yes - Built in Mic
Power Input	12V DC Socket (2.1mm)
On Board Recording	No
Alarm Input	No
Video Analytics	no
Operating Temperature	-30 ~ +55°
Dimensions (WHD)	Ø63x115mm
Weight (kg)	0.23
Warranty	3 Year Warranty