

Technical Data

Part Number: X4C2000MP-W
Product Group: CCTV
Product Type: IP Dome Camera



Xvision 2MP H265+ Micro Dome IP Camera, 2.8mm, 15m IR, 120dB WDR, Built in Mic

Model: X4C2000MP-W	
Style	Dome Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	Yes
Mounting Type	Wall or Ceiling
Sensor	1/2.8" Megapixel CMOS Sensor
On Board Camera Functions	Automatic White Balance, Automatic Gain Control, Automatic Electronic Iris, DNR, 120dB WDR, Starlight, Video Analytics, Backlight Compensation
Resolution	1080P

Technical Data

Lens Type	Fixed
Lens Size	2.8mm
Viewing Angle	99°
Night Vision	15m IR
Minimum Illumination	0.01 Lux
Video Compression	H265+
Video Streams	Triple Stream
Video Resolution & Frame Rates	1920x1080 - 25fps 1280x960 - 25fps 1280x720 - 25fps
Video Bitrate	8Kbps - 8Mbps
Network Connection	RJ45 Socket (10/100)
Network Protocols Supported	TCP/IP, HTTP, DHCP, DNS, DDNS, RTP/RTSP, PPPoE, SMTP, NTP, UPnP, SNMP, HTTPS, FTP
Onvif	Yes
Power Over Ethernet (PoE)	Yes
Power Consumption	<7W
Audio Input	Yes – Built in Mic
Power Input	12V DC Socket (2.1mm)
On Board Recording	Yes – Micro SD Card (Max 128GB)
Alarm Input	No
Video Analytics	Yes - Perimeter Intrusion Detection, Line Crossing Detection, Stationary Object Detection
Operating Temperature	-30 ~ 55°
Dimensions (WHD)	Ø119x65mm
Weight (kg)	0.30
Warranty	3 Year Warranty