

Technical Data

Part Number: X4C5000V-W

Product Group: CCTV

Product Type: IP Dome Camera



Xvision 5MP H265+ Vandal Dome IP Camera, 2.8mm, 40m IR, Starlight

Model: X4C5000V-W	
Style	Dome Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	Yes
Mounting Type	Wall or Ceiling
Sensor	1/2.7" Megapixel CMOS Sensor
On Board Camera Functions	Automatic White Balance, Automatic Gain Control, Automatic Electronic Iris, DNR, Starlight, Backlight Compensation
Resolution	5MP
Lens Type	Fixed
Lens Size	2.8mm
Viewing Angle	103°

Contact: 0208 689 9999 Email: customerservies@y3k.com

Technical Data

Night Vision	40m IR
Minimum Illumination	0.05 Lux
Video Compression	H265+
Video Streams	Dual Stream
Video Resolution & Frame Rates	2592x1944 - 15fps 2592x1520 - 20fps 2048x1520 - 25fps 1920x1080 - 25fps 1280x960 - 25fps 1280x720 - 25fps
Video Bitrate	256Kbps - 8Mbps
Network Connection	RJ45 Socket (10/100)
Network Protocols Supported	TCP/IP, HTTP, DHCP, DNS, DDNS, RTP/RTSP, PPPoE, SMTP, NTP, UPnP, SNMP, HTTPS, FTP
Onvif	Yes
Power Over Ethernet (PoE)	Yes
Power Consumption	<7W
Audio Input	Yes – Built in Mic
Power Input	12V DC Socket (2.1mm)
On Board Recording	Yes – Micro SD Card (Max 128GB)
Alarm Input	No
Video Analytics	No
Operating Temperature	-30 ~ 55°
Dimensions (WHD)	Ø100x90mm
Weight (kg)	0.36
Warranty	3 Year Warranty

Contact: 0208 689 9999 Email: customerservies@y3k.com