

EVEREADY®

GLS

- 2,000hr Lamp Life
- Clear Finish
- UV Stop Glass
- Dimmable
- Internal Fuse
- B22 & E27 Caps
- 40W - 150W Replacements



GLS - 2,000 HOURS

Box Code	Blister Code	Finish	Cap	Watt. & Equiv.	Lumen	Colour Temp.	Dimmable	Lamp Dims. (mm)	In/Out Box	In/Out Blister
S10133	S11877 (2pk)	Clear	E27	30W/40W	405lm	2700K	✓	55x90	10/100	10/100
S10132	-	Clear	B22	30W/40W	405lm	2700K	✓	55x90	10/100	-
S10135	S11880 (2pk)	Clear	E27	46W/60W	750lm	2700K	✓	55x90	10/100	10/100
S10134	S11879 (2pk)	Clear	B22	46W/60W	750lm	2700K	✓	55x90	10/100	10/100
S10137	S11882 (2pk)	Clear	E27	77W/100W	1320lm	2700K	✓	60x105	10/100	10/100
S10136	S11881 (2pk)	Clear	B22	77W/100W	1320lm	2700K	✓	60x105	10/100	10/100