



45W
45W PANEL DRIVER-FLICKER FREE

SKU:6270

5 YEARS
WARRANTY



Technical Information

Watts: 45

Warranty (Years): 5

Body Type: ABS Plastic

Operation Temperature: -25 to +50°C

IP Rating: IP20

Input Power: AC:200-240V

Dimmable: No

Features

- ✓ High quality capacitors for better case temperature
- ✓ EMC Compliant
- ✓ SELV & LVD Compliant
- ✓ Thermal overload and Short circuit connection built in
- ✓ Constant current LED drivers
- ✓ Isolated Driver for safer operation and extended lifetime
- ✓ Efficient Operation at transient operating conditions
- ✓ Warranty from 2 to 5 Years

Packaging

Unit Details

Gross Weight(GW) Kgs	0.152
Length(Box)mm	35
Width(Box)mm	60
Height(Box)mm	160
Unit CBM	0.000336

Listing Details

EAN Code	3800157614436
Commodity Code	8504409090

Master Box Packaging

Master Box Qty (Pcs Per Carton)	50
---------------------------------	----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES