



CARBON™ OPEN FRAME RACK

CR25U40001

Open frame rack allows fast and easy IT infrastructure deployments

The CR25U40001 4-post rack can be customized with compatible accessories to meet specific requirements. The rack ships knock-down; assembly is required. It is covered by a 5-year limited warranty.

FEATURES

- Rack Type: 4-post Open Frame 19" Rack
- Height: 25U
- Stationary Capacity: 1323 lbs
- Mounting Depth: 22" to 40"
- Mounting Hole Type: Square
- Warranty: 5 Years

TYPICAL APPLICATIONS

- Low Cost Builds
- Servers and Networks
- Open Equipment Access



SPECIFICATIONS

PHYSICAL	
Rack Height	25U
Color	Black RAL 9005 powder coat paint
Rack Angle Mounting Hole Type	Square Mounting Holes
Number of posts	4
Weight Capacity - stationary load (lbs)	1323

PHYSICAL - CONT.	
Weight Capacity - stationary load (kg)	600
Max. Mounting Depth (in)	40
Max. Mounting Depth (mm)	1016
Min. Mounting Depth (in)	22
Min. Mounting Depth (mm)	558.8

CARBON™ OPEN FRAME RACK

CR25U40001

SPECIFICATIONS CONT.

PHYSICAL - CONT.

Max. Dimensions (WxHxD in)	23.6 x 47.8 x 41
Max. Dimensions (WxHxD mm)	600 x 1215 x 1049
Min. Dimensions - WxHxD (in)	23.6 x 47.8 x 23.5
Min. Dimensions - WxHxD (mm)	600 x 1215 x 592
Net Weight (lbs)	57.6
Net Weight (kg)	26.1
Shipping Packaging Type	Knock down
Shipping Dimensions (WxHxD) (in)	7.3 x 5.9 x 60.6
Shipping Dimensions (WxHxD) (mm)	18.5 x 15.0 x 154.0
Shipping Weight (lbs)	65.9
Shipping Weight (kg)	29.9

SPECIAL FEATURES

Numbered Rack Units	Yes
Leveling Feet	Included
Rolling Casters	Optional
Cable Management	Toolless Mounting Slots and Cable Rings Included
PE Grounding Point	Yes



CERTIFICATIONS

Approvals	DIN41491, DIN41494, EIA/ECA-310-E, IEC-60297-3-100, RoHS
-----------	----------------------------------------------------------

WARRANTY

Product Warranty	5 Years Limited
------------------	-----------------