



## CPUDC1U2000 Universal Power Adapter

Your mobile AC adapter for portable electronic equipment.

The CPUDC1U2000 Universal Power Adapter with USB 2.1 Quick Charge Technology can be used as a replacement or spare DC power adapter for electronics such as portable DVD players and other A/V products, tablets, and many other electronic devices.

The CPUDC1U2000 with 2000mA supports voltages of 3V, 4.5V, 6V, 9V, and 12V with both positive and negative polarity settings. Seven (7) adapter tips assure compatibility with most popular electronics. The CPUDC1U2000's convenient DC plug can be used with a DC power port (cigarette lighter outlet) in a car, boat, or other vehicles with a port. The 5 ft. cord provides flexibility in where you operate your electronic equipment.

It is equipped with one (1) 2.1A USB port for charging tablets (including the iPad), smart phones, MP3 players, and digital cameras.

A One-Year Warranty ensures that this product has passed our highest quality standards in design, assembly, material and workmanship.

### Typical Applications

- Cameras
- MP3 Players
- Smartphones
- Portable AV Products

### Features

- 2000mA Universal Power Adapter
- Selectable Voltages: 3V, 4.5V, 6V, 9V, and 12V DC
- 7 Adapter Tips w/5 ft. Cord
- Quick Charge Technology
- (1) USB 2.1 Amp Charging Port
- Compact Design with DC Plug
- 1-Year Warranty

# CPUDC1U2000 Universal Power Adapter

Your mobile AC adapter for portable electronic equipment.

GENERAL	
Product Type	Universal Power Adapter
INPUT	
Voltage	10.5Vdc - 15.5Vdc
Plug Type	12Vdc Auto Power Port
Plug Style	Automotive
OUTPUT	
Output Power	2000mA
Output Voltage (Selectable)	3V, 4.5V, 6V, 9V, 12Vdc
USB Charge Port - Total	1
USB Charging Amperage	2.1A
Adapter Tips (Qty.)	7
Output Cord Length (ft.)	5
INDICATORS	
LED	Power On
PHYSICAL	
Color	Black
Form Factor	Direct Plug
Enclosure Construction	ABS
Dimensions (WxHxD) (in.)	2.1 x 4.8 x 1.1
Weight (lbs.)	0.26
ENVIRONMENTAL	
Operating Temperature	32°F to 95°F / 0°C to 35°C
Operating Relative Humidity	0% - 95% non-condensing
Storage Temperature	5°F to 113°F / -15°C to 45°C
Maximum Operating Elevation	10,000 ft / 3,000 m
Maximum Storage Elevation	50,000 ft / 15,000 m
CERTIFICATIONS	
Environmental	RoHS Compliant
WARRANTY	
Product Warranty	1 Year Limited