



CSP606U42A SURGE PROTECTOR

Protect home and office computers,
electronics, and home theater equipment

Designed for use in home and office, the CSP606U42A Surge Protector from CyberPower protects electronic devices from damage caused by power spikes and surges. It features six surge-protected outlets, two USB charge ports (4.2 Amps shared), and a six-foot power cord with a low profile plug. This surge protector, rated at 900 joules, is ideal for use video and audio equipment, cable and satellite equipment, game consoles, computers, laptops, and smartphones.

TYPICAL APPLICATIONS

- Consumer Electronics
- Personal Computers
- Phone/Fax/Modem
- Printers
- Stereos

FEATURES

- On/Off reset control switch and circuit breaker
- Ground and surge protected LED indicator
- Two USB charging ports (4.2A)
- 6 foot right-angle power cord
- Surge Protection: 900 Joules
- \$75,000 Connected Equipment Guarantee



SPECIFICATIONS

INPUT	
Input Voltage	125 V
Switch	Non Lighted On/Off - Reset
Plug Type	NEMA 5-15P
Plug Style	Right Angle, 45° Offset Right
Cord Length	6 ft
OUTPUT	
Outlet Type	NEMA 5-15R
Outlets - Total	6
USB Charge Port - Total	2
USB Charging Amperage	4.2A (shared)

SURGE PROTECTION & FILTERING	
Surge Suppression	900 joules
Maximum Surge Current	45,000 amps
Maximum Surge Current H-N	15,000 amps
Clamping Voltage L-N, L-G, N-G	500V
Response Time	< 1 nanosecond
CERTIFICATIONS	
Safety	UL1363, 1310, 1449 FCC DOE VI
Environmental	RoHS Compliant
WARRANTY	
Product Warranty	Limited Lifetime
Connected Equipment Guarantee	Yes
CEG Amount	\$75,000