# Wire Harness Tape -**Soft and Flexible Fleece Tape**

#### **HelaTape Protect 300**



HelaTape Protect 300 provides high noise reduction and media resistance.

#### Features and benefits

- Soft polyester fleece harnessing tape
- High noise reduction and very high resistance against abrasion
- Synthetic rubber based adhesive offers good heat and media resistance
- High temperature stability from -40 °C to +105 °C
- Material is very flexible and tearable by hand
- · Excellent ageing resistance and stable against rotting

# Wire Harness Tape -**High Noise Reduction Tape**

#### HelaTape Protect 1500



HelaTape Protect 1500 is extremely soft and offers very high noise reduction.

#### Features and benefits

- High quality polyamide velours harnessing tape
- Highest noise reduction and very high resistance against abrasion
- Acrylate based adhesive offers very good heat and media resistance
- High temperature stability from -40 °C to +130 °C
- Material is extremely soft and very flexible
- Excellent ageing resistance, stable against rotting

MATERIAL	Polyester (PET)		
<b>Operating Temperature</b>	-40 °C to +105 °C		
Adhesion to Steel	2 N/10 mm		
Adhesion to Backing	2 N/10 mm		
Elongation at break	10 %		
Breaking Strength	30 N/10 mm		

	/
HF	RoHS

Polyamide (PA)		
-40 °C to +130 °C		
2.5 N/10 mm		
2 N/10 mm		
50 %		
100 N/10 mm		



### HelaTape Protect 300

ТҮРЕ	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-PROTECT300	0.30	19.0	25.0 m	Black (BK)	712-10001

All dimensions in mm. Subject to technical changes. Minimum Order Quantity (MOQ) may differ from package content.

### HelaTape Protect 1500

ТҮРЕ	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-PROTECT1500	1.50	25.0	4.0 m	Black (BK)	712-10000

All dimensions in mm. Subject to technical changes Minimum Order Quantity (MOQ) may differ from package content.

402