

AWM 20276 80°C 30V VW-1 HIGH SPEED HDMI® CABLE WITH ETHERNET

NOTE:

1. CABLE: 28AWG(1/0.32BC),UL20276,AL+B+D-FOIL,[(#28\*1P+D+FAM)\*5PCS+#28\*4C],  
BLACK COLOR,OD=7.3±0.2mm,PVC JACKET.

2. LENGTH: L.

3. CONNECTORS: HDMI(M)\*2PCS(BLACK INSULATOR)(SHELL GOLD PLATED).

4. MOLD: MOLDING TYPE.

5. CONTACTS:

HDMI(M)	1	3	2	4	6	5	7	9	8	10	12	11	14	19	17	13	15	16	18	64
HDMI(M)	1 3 PAIR		2 G	4 6 PAIR		5 G	7 9 PAIR		8 G	10 12 PAIR		11 G	14 19 PAIR		17 G	13 15 16 18 4C				64 SHELL


6. Test machine test condition.

A.100% OPEN,SHORT&INTERMITANCE TEST.

B.CONDUCTOR RESISTANCE:2ohms MAX:

C.INSULATION RESISTANCE:10MΩ Min/,10ms:

7. ALL MUST BE MEET ON ROHS COMPLIANT.



PACKING: 1PCS/OPP BAG+LABEL

COMPANY			ITEM NO.			NO	F001-21-03099-A				SCALE	1:1
REVISION	DATE	DISCRIPTION	DRAWN BY	Yuwenming						UNIT(mm)		
REV.A/0	2019.06.24		DESIGNED BY	Chenrunming						PAGE	1/1	
			APPROVAL BY	Chenlianwei								