

Novopro LIG300

3 metre high, extendable width T-bar lighting stand,
with air cushioning and auto-lock ratchet system



Telescopic T-bar
Versatile lighting stand
All-metal construction
Auto-lock ratchet system
Air cushioning system
Easy & fast setup



Auto-lock ratchet and air cushioning system
for safe & easy operation

- Premium grade lighting stand - engineered to a high standard
- Telescopic T-bar for wide angle lighting dispersion
- 8 x integral lighting fixture points with thumb screws included
- All metal stand construction
- Up to 3 metre stand height
- Uses the industry standard, 35mm Ø top pole for universal compatibility
- Stand height: 1900mm – 3000mm / 74.8 – 118 inches
- T-Bar width: 1500mm – 2280mm / 59 – 89.7 inches
- Maximum load: 30Kg / 66lb (60Kg / 132lb for the main stand – but a 30Kg / 66lb limit for the T-Bar section)
- Material: Ø 35mm / 1.37 inches aluminium pole and steel legs
- Surface and colour: black powder coated
- Weight: 8.5Kg / 18lb 11oz

The Novopro LIG300 lighting stand has been designed for ease of use as well as safety. The stand has the patented auto-lock ratchet and air cushioning system which allows you to adjust the height and lock the stand to that height without the usual slipping and inconvenience of standard lighting stands.

Kit includes the following:
LIG300 lighting stand
LIG300 telescopic T-bar
Male & female thumb screws
Instruction manual

EAN barcode: 5060473244832

novopro

Designed & engineered in the UK by working performers

VISIT OUR WEBSITE FOR THE COMPLETE PRODUCT RANGE
www.novopro.co.uk

SEE
MORE
ONLINE