

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0369200602

Status:


Active

Overview:

Pico-EZmate and Pico-EZmate Slim Wire-to-Board Connector Systems

Description:

Pico-EZmate-to-Pico-EZmate Off-the-Shelf (OTS) Cable Assembly, 1.20mm Pitch, Single Row, 150.00mm Length, 6 Circuits, Black



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	36920
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Pico-EZmate-to-Pico-EZmate
Overmolded	No
Overview	Pico-EZmate and Pico-EZmate Slim Wire-to-Board Connector Systems
Product Name	Pico-EZmate
Type	Discrete Wire Assembly
UPC	193264110575
Physical	
Cable Length	150.00mm
Circuits (Loaded)	6
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	1.824/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	1.20mm
Plating min - Mating	0.100µm
Plating min - Termination	0.100µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.60-0.70mm
Wire Size AWG	28
Wire/Cable Type	UL 1571
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	50V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	369200600-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per

-ED/88/2018 (15

January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

36920 Series

Mates With

PicoEZmate Header 78171

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION