

SONICHEK™ PRO

Applications

- Quickly & accurately measure sound level
- Monitor workplace equipment
- Aids in installation of alarm and home theater equipment
- Test noise proofing environments

Features

- Designed according to IEC651 (Type 2) and ANSI S1.4 (Type 2) standards
- A/C weighted measurement reads 30 to 130dB
- Segmented bar graph
- Selectable FAST or SLOW read delay
- Frequency range 31.5Hz to 8kHz
- Accuracy: $\pm 1.5\text{dB}$ (94dB @ 1kHz)
- Min/Max hold
- Automatic backlit display
- 3 year warranty

