
SAC 1 Way Masthead Amp + PSU Kit 10-25dB

Product code: AE5031

SAC 1 input 1 output variable wideband 470 ~ 790MHz masthead amplifier. 17-32dB variable gain. All ports DC powered. kit includes PSU.

Specifications:

- All ports DC powered
- Fully shielded with F type connectors
 - LTE/4G Protected
 - Tight seal waterproof housing
 - SMD circuit technology design
- High output capability with low noise
- Easy to install and convenient to use
 - Number of inputs: 1
- Input frequency band: UHF - Input channels: 21-60
- Frequency range: 470-790MHz - Gain(variable): 10-25dB
 - Noise Figure: 3dB - Max output: 102dBuV
- DC output: 12V 100mA - Power rating: 220~240V/50Hz
- Insertion loss: 1dB - Operative temperature: -10°C ~ +40°C
- Contents: 1 x Amp, 1 x PSU, 1 x reusable tie-wrap, 2 x screws
 - Dimensions: 155x180x60mm - Weight: 1kg

