
SAC 2 Way Masthead Amp + PSU Kit 10-25dB

Product code: AE5032

Specifications:

- Dimensions: 155x180x60mm - Weight: 1.1 KG
- SAC 1 input 2 output variable wideband 470 ~ 790MHz masthead amplifier. 15-30dB variable gain. All ports DC powered. kit includes PSU.
 - All ports DC powered - Fully shielded with F type connectors
 - LTE/4G Protected - Tight seal waterproof housing
 - SMD circuit technology design - High output capability with low noise
 - Easy to install and convenient to use - Number of inputs: 1
 - Number of outputs: 2 - Input frequency band: UHF
 - Input channels: 21-60 - Frequency range: 470-790MHz
 - Gain(variable): 10-25dB - Noise Figure: 3.8dB
 - Max output: 102dBuV - DC output: 12V 100mA
 - Power rating: 220~240V/50Hz - Insertion loss: 1dB
 - Operative temperature: -10°C ~ +40°C - Short-circuit protection: yes
 - Contents: 1 x Amp, 1 x PSU, 1 x reusable tie-wrap, 2 x screws

