


Type	Size	Description	Part No.
Incandescent	T5 (T-1½)	Wire Terminal Lamp	(see table)



Drawing not to scale
All dimensions in mm

PHOTOMETRY DATA

Farnell Part No.	SLI P/N	Lamp Rating	Test Volts	Current (mA)			Light Output (Lm)			Fil Shape	Life (Hrs)
				Min	Nom	Max	Min	Nom	Max		
328893	673BS	6V 0.36W	6.0	50	55	60	0.8	1.0	1.2	C-2R	10000
329900	690BS	14V 0.56W	14	33	37	41	1.2	1.6	2.0	C-2F	5000
328911	682BS	14V 0.7W	14	45	50	55	2.2	3.0	3.8	C-2F	1000
328923	687BS	24V 1W	24	36	40	44	2.2	3.0	3.8	C-2F	10000
328935	688BS	28V 1.12W	28	36	40	44	3.4	4.5	5.6	C-2F	4000

NOTES:

- Lead wires 0.25mm diameter x 25.4mm MIN. long, with tinned finish.