

In-line Switch Model PL10018

Specification	
Description	Material
Box base and cover	Nylon
Terminals	Brass
Cover screw	Mild steel nickel plated
Cord grip screw	Mild steel nickel plated
Terminal Screw	Brass

Voltage	Current Rating	Standard
250V AC	2A	IEC61058-2-1

Conditions of use

1. Ambient temperature in the range -5°C to $+40^{\circ}\text{C}$, the average value over 24 hours not exceeding 25°C .
2. Situation not subject to exposure to direct radiation from the sun or other source of heat like to raise temperatures above the limits specified in 1.
3. Altitude not exceeding 2000 metres above sea level;
4. Atmosphere not subject to abnormal pollution by smoke, chemical fumes, rain, spray, prolonged periods of high humidity or other abnormal conditions.



Important Notice : This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.