

18V Angle Grinder 125mm BL LXT

DGA513Z

DGA513 is a 125mm, slide switch, variable speed angle grinder powered by 18V LXT lithium-ion battery.

18V Angle Grinder 125mm BL LXT



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	18 v
Battery Quantity (5.0ah)	0
Bore Diameter	22.23 mm
Max Wheel Thickness	7.2 mm
Noise sound pressure	79 dB(A)
Noise K factor	3 dB(A)
Max Wheel Diameter	125 mm
No Load Speed	3,000 - 8,500 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Surface Grinding	6.5 m/sec ²
Vibration: Disc Sanding	2.5 m/sec ²
Net weight	2.4 - 3.0 kg

USER BENEFITS

- Brushless motor
- Variable speed control dial.
- Anti-restart function.
- Electric brake
- On/off slide switch.
- Electronic current limiter for overload protection.
- Battery fuel gauge
- Ergonomic soft grip
- Automatic Torque Drive Technology: Automatically changes the cutting speed according to load condition for optimum operation
- Active Feedback Sensing Technology (AFT): Shuts down the tool to protect the user if the rotation speed suddenly slows down
- Removable dust covers
- Lock-on function
- Soft start.



RELATED PRODUCTS

(Recon

■ OTHER