

SC-5MP-D-W

Dome Style
5MP Day/Night
All-Weather
CCTV Camera



Professional - 24/7 monitoring and recording CCTV facility



Staff & worker
security



Warehouse &
factory security



Remote &
out of bounds



Residential
security

Affordable Night Day CCTV Solutions - For Residential and Business

Looking for a low-cost but effective night/day, all weather camera with proven CMOS technology?

The exciting **SC-5MP-D-W** is a fully featured, Dome form-factor colour CCTV camera that can be mounted internally or externally, thanks to its weather resistant, IP66 rated housing.

Fully HD, courtesy of its latest generation CMOS imaging with up to 2592x1944 resolution, up to 30 Frames Per Second (FPS) for fluid playback, night and day. Fully compatible with standard analog DVR/ NVRs with coax interface.

Need 24/7 security? This next-generation CCTV camera offers advanced Infra-Red (IR) imaging so it can display and record in complete darkness, up to around 20 metres.

Easy to install, ideal for ceiling or wall placement with a fully adjustable housing and of course wide-angle optics for better area coverage.

specifications:

High Resolution 5-Megapixel CMOS Optics

HD Resolutions: 2592x1944, 2560x1440, 1920x1080

Multi-Coated Glass Optics - 3.6mm wide angle viewing

Auto White Balance - Ideal for Multiple Lighting Options

Advanced Night Vision - IR illumination Up To 20 metres

OSD Menu System - Easy Setup via NVR/DVR

Ideal For Internal or External Deployment - IP66 Rated

Dimensions: 93 x 74mm (approx)

Weight: 400grams (approx)



blupont

Copyright 2019 Blunpont
E&OE. All Trademarks Acknowledged
Product subject to change. v1.0