

PA84NRSV

Terminal block with integrated cable clamp, for snap-in fixing on chassis (without screw)



SPECIFICATION

Tab Size (mm)	6.3x0.8
Terminal Material	Zinc-plated steel
Body Material	Natural polyamide
UL94 Rating	UL94V2
Max Conductor Size (Sq mm)	1.5
Min Conductor Size AWG	18
Max Conductor Size AWG	14
Max Current (A)	16
Max Voltage (V)	450
Min Temperature Rating °C	-5
Max Temperature Rating °C	125
Height (mm)	23
Width (mm)	29
Length (mm)	66
Comments	Photo is just a representative of terminal block