

Accessory

Temperature scanner HL Scan

EAN 4007841 014919

STEINEL[®]
Intelligent technology



CE



VDE

Function description

Insurance cover for temperature-sensitive workpieces. Temperature scanner HL Scan monitors workpiece temperature by a beam of LED light. An acoustic and visual signal warns the user when temperature exceeds or falls below the permissible limit. For the HL 1920 E, HL 2020 E as well as the Professional HG 2120 E and HG 2320 E tools.

Technical specifications

Temperature measurement range	0-300°C, adjustment in 10°C steps	Dimensions (L x W x H)	147 x 51 x 44 mm
Temperature scan	via Sensor	Mains power supply	9 V
Optimum distance from workpiece	15 cm	PU1, net weight	0,143 kg
Work-area marking	with LED light beam	Manufacturer's Warranty	3 years
Emission level	adjustable (0.85 / 0.90 / 0.95)	PU1, EAN	4007841014919
Power supply, detail	Batteries (included)		