



Cut Resistant Gloves In Use



Specifications:

Electrical PropertiesTypical ValuesTest Procedures/MethodSurface Resistivity:< 1 x 109 ohms</td>Surface Resistivity Meter

Product Description

Fabric: Ultra-high-molecular-weight polyethylene

Confifuration: Elastic Wrist Liner Color: Grey Coating Color: White

Shelf Life: Functional: 1 year

Functional Properties

Thickness on Coated Area 1.0 mm (± 0.2) Thickness Gage (Dial Type/

Digimtic Type)

Abrasion Resistance (Revs) 4 - Performance Level EN 388: 2003
Blade Cut Resistance 5 - Performance Level EN 388: 2003
Tear Resistance (N) 4 - Performance Level EN 388: 2003
Puncture Resistance 2 - Performance Level EN 388: 2003

Item	Size	Length*	
<u>17131</u>	Small	8-1/4"	210 mm
<u>17132</u>	Small	8-5/8"	220 mm
<u>17133</u>	Medium	9"	230 mm
<u>17134</u>	Large	9-1/2"	240 mm
<u>17135</u>	X-Large	9-7/8"	250 mm
<u>17136</u>	XX-Large	10-1/4"	260 mm

Sold in Pairs

*Length is measured from the tip of the fingers to the bottom of the glove.

Tolerance: ±3/8"

Glove Laundering

For proper operation, the ESD Gloves must be laundered periodically. Woolite works well. Liquid detergents are better than dry in that there is less caking and frictional wear. Launder glove in cool or warm water, tumble dry with low heat or hang dry. Machine washing works well if using a standard house machine on gentle cycle. It is not recommended to launder these gloves in heavy industrial laundry machines as it will lead to premature wear. Gloves should be tumbled dry using low heat. DO NOT BLEACH. After laundering, verify < 1 x 10⁹ ohms.

Specifications and procedures subject to change without notice.

ESD CUT RESISTANT GLOVES

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: <u>Desco.com</u> PHONE (909) 627-8178

DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407 PHONE (781) 821-8370

DRAWING NUMBER 17131 DATE: October 2019

Country of Origin: Israel

DESCO