

Thermal transfer printer : TT431

Thermal Transfer Printer 300 dpi, Article number: 556-00400

 Add to watchlist



 Images (3)



Features

- Small to medium volume single sided printing
- Print on HellermannTyton cable markers and labels
- Uses standard ribbons
- Barcodes: standard and 2D
- Print speed up to 150 mm/s
- Adjustable label sensor
- Multiple language selection
- Windows drivers: 32/64 bit for Windows Vista, Windows 7, 8 and 10

Certifications & Approvals

Contact 



Application

The TT431 thermal transfer printer is perfect for printing on HellermannTyton materials such as self-adhesive labels, shrinkable tubing and identification tags. Thanks to its low weight and compact construction, the TT431 integrates seamlessly into any workstation. It is easy to use due to its intuitive colour LCD touch display and clear status messages which can be shown in multiple languages. The optional cutter and perforator make this printer ideal for a wide range of applications. 300 dpi resolution ensures that barcodes, warning symbols, logos and text are as sharp as they can be.

TT431, Small to medium volume printing is suitable for following markets and industries



More products in this product group

[Thermal transfer printer >](#)

Base Data


Colour	Grey (GY)
Pack Cont.	1 pc.
Package Quantity per	carton
PART DESCRIPTION	TT431-DIV-GY
Product Family	TT431, Small to medium volume printing
Product Group	Thermal transfer printer
Short Description	Thermal Transfer Printer 300 dpi

Product Dimensions

Depth (D)	322 mm
Height (H)	189 mm
L x H x W	322 mm x 187,5 mm x 253 mm
Label Height Max (metric)	4000 mm
Label Height Min (metric)	5.00 mm
Label Width Max (imperial)	4.16 "
Label Width Max (metric)	105.7 mm
Label Width Min (imperial)	.39 "
Label Width Min (metric)	10.00 mm
Label Width min - max	10 - 105.7 mm
Print Method	Thermal transfer
Width (W)	253 mm

Material and Specifications

Contact

ELV compliant (Article 4 - 2)	YES
Hazardous good	No
Interfaces	USB 2.0, Ethernet 10/100 Base T, RS232
Material	Various (DIV)
Max. Print Width	105.70 mm
Print Head Type	300 dpi, flat type
Print Speed	up to 150 mm/s
Printer Memory	256 MB RAM
Specifications	
Specifications	2014/35/EU, DIN EN 55024:2011-09, DIN EN 55024:2016-05, DIN EN 55032:2012-12, DIN EN 55032:2016-02, DIN EN 55032 rectification 1:2013-04, DIN EN 61000-6-2:2006-03, DIN EN 61000-6-2 rectification 1:2011-06, EN 55024:2011-09, EN 61000-6-2, FCC eCFR 47 FCC part 15 - subpart B, limit class A
Supported Barcodes, Printer	Standard and 2D
UL-File Number	[cULus§2§

Logistics and Packaging

More Information

ETIM 6.0	EC001672
ETIM 7.0 Key	EC001672

Accessories

TT Printer Adapter

556-00012

Thermal Transfer Printer Accessories



TT430/TT431 Print Roller

556-00454

Accessories for Thermal Transfer Printer TT430/TT431



TT430/TT431 300dpi Printhead

556-00453

Accessories for Thermal Transfer Printer TT430/TT431



P430 Perforator

556-00456

Thermal Transfer Printer Accessories



TagPrint Pro 3.0 EMEA

556-00051

Labeling Software




TT External Reel Holder

556-00451

TT430 External Reel Holder



Show all 

© HellermannTyton 2019