



28" LED UHD MONITOR

SPECIFICATION	LED-4K-28P-O
DISPLAY	
Screen Size	28"
Backlight Type	LED
Aspect Ratio	16:9
Brightness (Max.)	300 cd/m ²
Contrast Ratio (Max.)	3000:1
Resolution	3840 x 2160 @ 60Hz, downwards compatible
Response Time (Max.)	5ms (G2G)
Viewing Angle (Horizontal/Vertical)	170°/160° (CR>10)
Colour Support	16.7M
Filter	3D combo
CONNECTOR	
HDMI 2.0 Input	2x
DP 1.2 Input	2x
CABINET	
Front Cover	Plastic case
Back Case	Plastic case
Stand	Plastic case
POWER	
Power Consumption	Typical 40W
Type	DC 12V, 5A
FEATURES	
Plug & Play	Supported
Free Sync	Yes
PIP & PBP	None
HDCP	Version 2.2
Remote Control	Yes
VESA Mount	100x100mm
Audio	2x 3W
Dimensions	Monitor with Stand 659.2x190x472.7mm
Weight	Gross Weight: 7.5kg Net Weight: 5.8kg