

RJ12 6p6c keystone socket



RJ12 6p6c keystone socket (KSH66)

This keystone offers a convenient way to incorporate RJ11 or RJ12 socket into a variety of cabling situations. With its standardised dimensions, it can be used for easy snap-in mounting in e.g. a keystone patch panel, faceplate or surface-mount box.

Features

- RJ11 and RJ12 high quality keystone socket
- Easy to use cable retention facility
- LSA+/110 dual type IDC contacts suitable for cable with solid wire cores measuring 26-24 AWG / 0.40-0.51mm
- Also available in D Universal and Panel Mount versions

Specifications

- Weight: 8g approx.
- Dimensions: 36.4 x 22.8 x 22.3mm approx.
- Colour: black or white
- Material:
 - Housing: UL rated ABS
 - Socket contact: gold-plated over nickel over phosphor bronze
 - IDC housing: PC/ABS
 - IDC contact: tin-plated phosphor bronze
- Operating temperature: -20°C to 80°C

Packaging: Supplied in individual polybags then in bags of 20

EAN: KSH66bk 5055386507723
KSH66bkDpm 5055386507747

KSH66wh 5055386507730
KSH66whpm 5055386506658

Commodity Code: 85444290

