

Product Specification Sheet



18W

VT-618RD 18W LED PREMIUM PANEL WITH SAMSUNG CHIP COLORCODE:3000K ROUND

Lumens 1500 Beam Angle 120

Dimensions ?225x12mm

Warm White SKU:718









Technical Information

Output Voltage:	DC:36-72V
Watts:	18
Lumens:	1500
Shape:	Round
Beam Angle:	120
Cutting Size:	?210mm
Unit Color:	White
Body Type:	Aluminium
Long life:	30.000 Hours

 LED Chip Type:
 SMD

 IP Rating:
 IP20

 Dimmable:
 No

 Warranty (Years):
 5

 PF:
 >0.6

 CRI:
 >80

 Operation Temperature:
 -20°C to 45°C

 Input Power:
 AC:85-265V,50/60Hz

 Sensor Compatibility:
 Yes

Features

- Contemporary & Elegant Design
- Highly Efficient LED Samsung Chip
 - Easy to install Plug & Play
- High-quality power driver ensures a reliable lifetime
- Controlled Glare rating values for comfortable commercial applications
- No Lead or Mercury content hence Environment-friendly
- Easy to install & Low Maintenance
- Application Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc





Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

 Gross Weight(GW) Kgs
 0.515

 Unit CBM
 0.002532

Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 20

 Qty Per Pallet
 480

Listing Details

 EAN Code
 3800157641746

 Commodity Code
 9405403990



Dispatch within

Www.vtacexports.com

OUR PRODUCTS ARE CURRENTLY SOLD IN OVER 70 COUNTRIES