



24W

VT-624RD 24W LED PREMIUM PANEL WITH SAMSUNG CHIP
 COLORCODE:3000K ROUND

| | | |
|-----------------------|--------------------------|--------------------------------|
| Lumens 2000 | Beam Angle 120 | Dimensions ?300x12mm |
|-----------------------|--------------------------|--------------------------------|

Warm White
 SKU:724



Technical Information

| | | | |
|-----------------|---------------|------------------------|--------------------|
| Instant Start: | 0-100% lt1Sec | LED Chip Type: | SMD |
| Output Voltage: | DC:54-100V | IP Rating: | IP20 |
| Watts: | 24 | Dimmable: | No |
| Lumens: | 2000 | Warranty (Years): | 5 |
| Shape: | Round | PF: | >0.9 |
| Beam Angle: | 120 | CRI: | >80 |
| Cutting Size: | ?280mm | Operation Temperature: | -20°C to 45°C |
| Unit Color: | White | Input Power: | AC:85-265V,50/60Hz |
| Body Type: | Aluminium | Sensor Compatibility: | Yes |
| Long life: | 20,000 Hours | | |

Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

| | |
|----------------------|---------|
| Gross Weight(GW) Kgs | 0.88 |
| Unit CBM | 0.00433 |

Listing Details

| | |
|----------------|---------------|
| EAN Code | 3800157641807 |
| Commodity Code | 9405403990 |

Master Box Packaging

| | |
|---------------------------------|-----|
| Master Box Qty (Pcs Per Carton) | 10 |
| Qty Per Pallet | 300 |

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES