



24W

VT-625SQ 24W LED ADJUSTABLE PANEL WITH SAMSUNG CHIP
COLORCODE:3000K SQUARE

Lumens 1800	Beam Angle 120	Dimensions 223x223x32mm
-----------------------	--------------------------	-----------------------------------

Warm White
SKU:742



Technical Information

Instant Start: 0-100% 1t1Sec	LED Chip Type: SMD
Watts: 24	IP Rating: IP20
Lumens: 1800	Dimmable: No
Shape: Square	Warranty (Years): 5
On/Off Cycles: >15000	PF: >0.6
Beam Angle: 120	CRI: >80
Cutting Size: 75-200mm	Operation Temperature: -20°C to 45°C
Unit Color: White	Input Power: AC:85-265V,50/60Hz
Body Type: Aluminium	Sensor Compatibility: Yes
Long life: 20,000 Hours	

Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	1.336224
Unit CBM	0.008755

Listing Details

EAN Code	3800157643115
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	280

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES