



6W

VT-607 6W LED PREMIUM PANEL COLORCODE:6400K ROUND

Lumens <b>420</b>	Beam Angle <b>120</b>	Dimensions <b>Ø120x12mm</b>
----------------------	--------------------------	--------------------------------

White  
SKU:4856

**2** YEARS  
WARRANTY

**SENSOR**  
COMPATIBLE



## Technical Information

Instant Start: 0-100% in 11s	Long life: 20,000 Hours
Output Voltage: DC 12-28V	LED Chip Type: SMD
Watts: 6	IP Rating: IP20
Lumens: 420	Dimmable: No
Shape: Round	Warranty (Years): 2
Beam Angle: 120	PF: >0.5
Output Current: 300mA	CRI: >80
Cutting Size: 110mm	Operation Temperature: -25 to +50°C
Unit Color: White	Input Power: AC:85-265V,50/60Hz
Body Type: Aluminium	Sensor Compatibility: Yes

## Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

## Unit Details

Gross Weight(GW) Kgs	0.2
Length(Box)mm	200
Width(Box)mm	140
Height(Box)mm	30
Unit CBM	0.00076

## Listing Details

EAN Code	3800230629777
Commodity Code	9405403990



## Master Box Packaging

Master Box Qty (Pcs Per Carton)	50
Qty Per Pallet	1600

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES