



VT-8019 PHOTO CELL SENSOR


Dimensions  
**35.5x46x44.1mm**

SKU:5081

**2 YEARS**  
**WARRANTY**

## Technical Information

Ambient Light:	Long life:	20,000 Hours
Time Delay:	IP Rating:	IP44
Detection Range:	Dimmable:	No
Unit Color:	Warranty (Years):	2
Body Type:	Input Power:	AC:220-240V,50Hz
Sensor Type:		Photocell



## Features

- ✓ Downlight series built with High quality COB LED chip
- ✓ Premium Quality Power Driver with high quality power factor correction
- ✓ Die cast aluminium housing with heat sink for optimum thermal mangement
- ✓ Multi faceted aluminium reflector for optimum light intensity
- ✓ Lumen efficiency range starting from 65lm/W up to 120LM/W
- ✓ Non-Flickering - No UV Radiation
- ✓ Low Maintenance and Easy Installation
- ✓ Available from 3W to 40W
- ✓ Applications - Residential, Showrooms, Hotels & Boutiques etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

## Unit Details

Gross Weight(GW) Kgs	0.07
Length(Box)mm	38
Width(Box)mm	65
Height(Box)mm	95
Unit CBM	0.000325

## Listing Details

EAN Code 3800157608015



## Master Box Packaging

Master Box Qty (Pcs Per Carton)	100
Qty Per Pallet	3000

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES