

DPB22-R11R

Reset mushroom head push button 1a 1b red cap



SPECIFICATION

| | |
|--|------------------------------|
| Button Head Material | PA66 V2 |
| Body Material | PA66 + 15% GF-VO |
| Locknut Material | PA66 V2 +15%GF |
| Button Head Lamp Colour | Red |
| Number of Contact Blocks | 2 |
| Switch Action | Latching |
| Shaft Style | Standard |
| Max Wire Size Single Strand (Sq mm) | 2.5 |
| Max Wire Size Multi Strand (Sq mm) | 1.5 |
| Min Temperature Rating °C | -10 |
| Max Temperature Rating °C | 65 |
| Panel Hole Size | 22.5mm |
| IP Rating | 56 |
| Product Sub Type | Twist to reset mushroom head |
| Product Type | Push button non-illuminated |
| Terminal Type | Screw clamp |