

Ink ribbon - THERMOMARK-RIBBON 110/50 - 0800687

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ink ribbon, for roll printer for printing product groups TML..., WML..., WML HF..., WML-FLAG..., WMT..., WMTB..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP..., EMLF..., PML..., and PMM..., width: 110 mm, color: black

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356644822
Weight per Piece (excluding packing)	83.900 g
Custom tariff number	96121010
Country of origin	China

Technical data

Dimensions

Length (b)	50 m
Width (a)	110 mm

General

Color	black
Material	Polyester

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	19140611
eCl@ss 4.0	24190100
eCl@ss 4.1	24190100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100

Ink ribbon - THERMOMARK-RIBBON 110/50 - 0800687

Classifications

eCl@ss

eCl@ss 6.0	19149200
eCl@ss 7.0	19149290
eCl@ss 8.0	19140611
eCl@ss 9.0	19140611

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001675
ETIM 5.0	EC001675
ETIM 6.0	EC001694
ETIM 7.0	EC001694

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43211612
UNSPSC 18.0	44103112
UNSPSC 19.0	44103112
UNSPSC 20.0	44103112
UNSPSC 21.0	44103112