
Go-glo

Datasheet

LED portable re-chargeable,
foldable floodlight (15W)



- Extremely versatile and powerful portable light for work / leisure use eg. camping, fishing, outside entertaining, motoring, garage, workshop, during power cuts etc.
- Supplied with plastic carry case, mains transformer and 3m car adapter cable
- Powered / charged by mains transformer or car battery
- Equipped with Samsung LEDs - super bright 1100 lumens at 100% output
- Superior aluminium PCB for efficient heat dissipation >35,000 hrs working life
- On/Off and 50%/100% output switches
- Battery life 3 hours at 100% / 6 hours at 50% with 3 hour re-charge
- IP54 rated and insulation class I (nb. Transformer = insulation class II, indoor only)
- Toughened glass cover and sturdy, lightweight aluminium frame, weighs only 1.1 kg



Go-glo

LED portable re-chargeable,
foldable floodlight (15W)

Datasheet

Specifications

Model No.	Input Power	Output Power	Size (mm) l x w x h	LEDs	Lumens max	CRI	Beam Angle	PF	Weight
GO-GLO15	18W	15W	220 x 170 x 40	Samsung 2835 x 20	1100	82	120°	>82	1.1 kg

CCT Range: WW (3000K - 3500K) NW (4000K - 4500K) PW (6000 - 6500K) CW (7000K - 7500K)

Temperature	Electrical Characteristics	Battery = Lithium 18650 4400 mAh
Storage: -30°C ~ +70°C	Input Voltage: AC 85 ~ 265V 50/60Hz	Duration @100%: 3 hours
Operating: -20°C ~ +65°C	Power Efficiency: > 0.82	Duration @50%: 5/6 hours
		Recharge time: 3 hours

Also included :

Mains transformer + 1.5m cable

Plastic carry case



Optional Colours

Blue



Green



Black



Also available in Silver, Orange and Yellow

