



**18W**

VT-819 18W LED WALL LAMP COLORCODE:4000K WHITE BODY,IP44

Lumens  
**1800**

Beam Angle  
**90**

Dimensions  
**600x100x42mm**

Day White  
SKU:8534

**2 YEARS**  
WARRANTY

**SENSOR**  
COMPATIBLE



## Technical Information

Watts:	18
Lumens:	1800
On/Off Cycles:	>15000
Beam Angle:	90
Unit Color:	White
Body Type:	Aluminium
Long life:	20,000 Hours
LED Chip Type:	SMD

IP Rating:	IP44
Dimmable:	No
Warranty (Years):	2
PF:	>0.5
CRI:	>80
Operation Temperature:	-25 to +50°C
Input Power:	AC:220-240V,50/60Hz
Sensor Compatibility:	Yes

## Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

## Unit Details

Gross Weight(GW) Kgs	1.608
Unit CBM	0.007168

## Listing Details

EAN Code	3800157638685
Commodity Code	9405403990

## Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	160

READY STOCKS IN

UK & EU



Dispatch within

24 Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

70

COUNTRIES