


HY115/16 FVSP

16 pole natural polyamide PA6.6 male and female plug and socket terminal block 11.5mm pitch 35a 450v



SPECIFICATION

Number of Poles	16
Body Material	Polyamide PA6.6
Colour	Natural
UL94 Rating	UL94V0
Glow Wire Resistance Test Temp	GWT750°C
Min Conductor Size (Sq mm)	6
Max Current (A)	35
Max Voltage (V)	450
Working Temperature	T150
Pitch (mm)	11.5
Height (mm)	18
Width (mm)	46.2
Length (mm)	226.5
Diameter (mm)	3.5
Comments	Male and Female
Terminal Screw Material	White zinc plated steel