

**TEMPO TPC 201610**

**Order symbol:** TPC 201610  
**Product nbr:** 5824001  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074086648  
**EI. number:**  
 Finland:

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Dimensions:	Length	Width	Height	Accessories:	
mm:	201	163	98	DH-3	DIN-35 Mounting rail
inch:	7.9	6.4	3.9	ARH 2320	DIN-35 Mounting rail
				FP 10674	

Materials:		Rating:
<b>Material:</b>	Polycarbonate	Ingress Protection (EN 60529): IP65
<b>Base colour:</b>	RAL 7035 -light grey	Impact Resistance (EN 62262): IK07/IK08
<b>Cover screws material:</b>	Polyamide	Electrical insulation: Totally insulated
<b>Cover colour:</b>	RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
<b>Cover screws colour:</b>	Grey	Flammability Rating: UL 746C 5"
<b>Gasket material:</b>	Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 960
		NEMA Class: NEMA 1, 4, 4X, 12

Temperatures:		Certificates:
<b>Temperature °C (short term):</b>	-40 ... 120 °C	SGS Fimko
<b>Temperature °C (continuous):</b>	-40 ... 80 °C	
<b>Temperature °F (short term):</b>	-40 ... 250 °F	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F	

Accessories:	
MP 2016	Mounting plate

