

**TEMPO TPCM 191209T**



**Order symbol:** TPCM 191209T  
**Product nbr:** 5824029  
**Description:** Enclosure, PC  
**Remarks:** Clear transparent cover

**EAN:** 6418074087133  
**EI. number:**  
**Finland:**

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

Dimensions:		Length	Width	Height	Accessories:	
mm:		187	122	90	MIV 10	DIN-35 Mounting rail
inch:		7.4	4.8	3.5	DH-3	DIN-35 Mounting rail
<b>Materials:</b>					FP 10674	
<b>Material:</b>		Polycarbonate			DPS 14553	Grey sealing plug set
<b>Base colour:</b>		RAL 7035 -light grey			<b>Rating:</b>	
<b>Cover screws material:</b>		Polyamide			Ingress Protection (EN 60529): IP65	
<b>Cover colour:</b>		RAL 7035 -light grey			Impact Resistance (EN 62262): IK07/IK08	
<b>Cover screws colour:</b>		Grey			Electrical insulation: Totally insulated	
<b>Gasket material:</b>		Polyurethane			Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Temperatures:</b>					Flammability Rating: UL 746C 5"	
<b>Temperature °C (short term):</b>		-40 ... 120 °C			Glow Wire Test (IEC 695-2-1) °C: 960	
<b>Temperature °C (continuous):</b>		-40 ... 80 °C			NEMA Class: NEMA 1, 4, 4X, 12	
<b>Temperature °F (short term):</b>		-40 ... 250 °F			<b>Certificates:</b>	
<b>Temperature °F (continuous):</b>		-40 ... 175 °F			SGS Fimko	
<b>Accessories:</b>						
MP 1912		Mounting plate				

