

TEMPO TPC 292411T



Order symbol: TPC 292411T
Product nbr: 5824008
Description: Enclosure, PC
Remarks: Clear transparent cover

EAN: 6418074086839
EI. number:
Finland:

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

| Dimensions: | Length | Width | Height | Accessories: |
|-------------|--------|-------|--------|--------------------------------|
| mm: | 289 | 239 | 107 | DR 265 DIN-35 Mounting rail |
| inch: | 11.4 | 9.4 | 4.2 | DR 215 DIN-35 Mounting rail |
| | | | | FP 10674 |

| Materials: | Rating: |
|---|--|
| Material: Polycarbonate | Ingress Protection (EN 60529): IP65 |
| Base colour: RAL 7035 -light grey | Impact Resistance (EN 62262): IK07/IK08 |
| Cover screws material: Polyamide | Electrical insulation: Totally insulated |
| Cover colour: RAL 7035 -light grey | Halogen free (DIN/VDE 0472, Part 815): 1 |
| Cover screws colour: Grey | Flammability Rating: UL 746C 5" |
| Gasket material: Polyurethane | Glow Wire Test (IEC 695-2-1) °C: 960 |
| | NEMA Class: NEMA 1, 4, 4X, 12 |

| Temperatures: | Certificates: |
|--|---------------|
| Temperature °C (short term): -40 ... 120 °C | SGS Fimko |
| Temperature °C (continuous): -40 ... 80 °C | |
| Temperature °F (short term): -40 ... 250 °F | |
| Temperature °F (continuous): -40 ... 175 °F | |

| Accessories: |
|---|
| MP 2924 Mounting plate |

