Scratch Brushes, Spid-Scratch Brushes, Spark Plug Brushes and File Cleaners

Scratch brushes with wooden core are available in different working widths (number of rows). Spid-scratch brushes are designed for use for narrow section workpieces or profiled surfaces.

Fill types: HB


OSG – Steel wire, hardened, straight.


INOX – Stainless steel wire, acid resistant, straight.

MES – Brass wire (Cu-Zn), crimped.

Fill types: SPID

LTE – Brass plated steel wire, tempered, single-wire, crimped. INOX – Stainless steel wire, acid resistant, crimped.





Applications:

Cleaning, rust removal and paint removal.

Spark plug brushes ensure that the sparks stay bright.

Fill types: ZK

BES – Bessemer steel wire,
crimped.

MES – Brass wire (Cu-Zn), crimped.

Application:

Cleaning of sparking plugs.


File cleaners are produced from wooden corps and carding band.

Fill type: HB

OSG – Steel wire, hardened, straight.

Applications:

Specially for cleaning of woodworking and metalworking files.





Scratch Brushes						ar eye tection!	Drahthandbürsten	
Dimensions/				Туре				
Abmessu	ngen							
L1	В	RH	L2	L3		0.30 OSG	0.30 INOX	0.30 MES
mm	mm		mm	mm		ArtNo.	ArtNo.	ArtNo.
290	22	2	140	25	HB 120	4093.0019	4093.0021	4093.0024
290	28	3	140	25	HB 130	4093.0025	4093.0027	4093.0030
290	32	4	140	25	HB 140	4093.0001	4093.0007	4093.0002
290	38	5	140	25	HB 150	4093.0037	4093.0039	4093.0003
200	00	•	1 10	20		1000:0007	1000.0000	1000.0

Spid-S	Scratch B	rushes			Wear eye protection!	Spid-Handbürsten		
Dimension	,				Туре			
Abmessun L1	gen B	RH	L2	L3		0.30 LTE	0.30 INOX	
mm	mm		mm	mm		ArtNo.	ArtNo.	
265	28	1	140	25	SPID	4099.6457	4099.6492	