

HAKO

FM2022-05



Packing List



FM2022 Hot Tweezer Tool (FM2022-02)



B2300 Heat Resistant Pad



Connecting Cable



FH200-03 Iron Stand A1519 Cleaning Sponge

Specifications:

FM2022 SMD Hot Tweezer Tool

Power consumption	140W (24V)
Temperature range	200 to 400°C
Tip to ground resistance	<2Ω
Tip to ground potential	<2mV
Heating element	Composite heater
Cord length	1.2m
Total length	148mm (with SOP 25L tip)
Weight	64g (with SOP 25L tip)

^{*} Total length and weight (w/o cord)

Tips (Pairs):

The FM2022 Conversion Kit does NOT come supplied with Tips. T16 Tips are available to purchase separately:

T16 Series

Chip



T16-1001 0.5I SMD Type

SOP



T16-1002 0.5C SMD Type



T16-1003 1L SMD Type




599B

Tip Cleaner

Recommended Extras:

T16-1004 2L




B2756

Tip Holder

T16-1013 3L



T16-1005 6L SMD Type



T16-1006 8L SMD Type





T16-1007 10L SMD Type



T16-1008 13L SMD Type



SMD Type



T16-1010 20L SMD Type



T16-1011 25L SMD Type



T16-1012 18L SMD Type

