

Packing List:



# **FX-888D**



FX-888D Station with British Power Cord + Instruction Manual



FX8801 Soldering Iron with T18-B Standard Soldering Tip



FH800 Iron Stand A1559 Cleaning Sponge A1561 Cleaning Wire



\* Also Available in Silver

## Specifications:

Model No.	FX-888D
Power consumption	70W
Temperature range	50 to 480°C
Temperature stability	±1°C at idle temperature (When set to 200 to 480°C)

FX-888D Soldering Station

Output voltage	AC 26V
Dimensions	100(W)×120(H)×120(D)mm
Weight	1.2kg

#### FX8801 Soldering Iron


Power consumption	65W (26V)
Tip to ground resistance	<2Ω
Tip to ground potential	<2mV
Heating element	Ceramic heater
Standard tip	Shape-B (No.T18-B)
Cord length	1.2m
Total length	217mm (with B tip)
Weight	46g (with B tip)

<sup>\*</sup> Total length and weight (w/o cord)

### Tips:

The FX8801 supplied with the FX-888D soldering station requires the T18 Series Tips which are available in a variety of shapes and sizes. Note: A Standard tip is included with this soldering station. Alternate tips may be purchased separately.

### Shape BC / C



T18-C05 Shape-0.5C



T18-C5 Shape-5C






T18-CSF25 Shape-2.5CS This type has good heat transfer with short tip end design, tinned



T18-C08 Shape-0.8C




T18-S6 Shape-S6




*6*0° 16.5




T18-C1 Shape-1C T18-C2 Shape-2C




T18-CF2 Shape-2C Tinned cut surface only




T18-C3 Shape-3C



T18-CF3 Shape-3C Tinned cut surface only




T18-C4 Shape-4C




T18-CF4 Shape-4C Tinned cut surface only

## Tips (Continued):


### Shape B



T18-B Shape-B



T18-BL Shape-BL




T18-S4 Shape-S4 Narrow-pitch Soldering Type (Shape S)




18-SB Shape-SB larrow-pitch Soldering Type Shape S)

### Shape D




T18-D08 Shape-0.8D




T18-D12 Shape-1.2D



T18-D16 Shape-1.6D



T18-D24 Shape-2.4D




T18-D32 Shape-3.2D




T18-DL12 Shape-1.2DL




T18-D24 Shape-2.4D



T18-D32 Shape-3.2D



T18-DL12 Shape-1.2DL



T18-S9 Shape-S9 Narrow-pitch Soldering Type (Shape S)

### Shape I/J/K



T18-I Shape-I



T18-BR02 Shape-0.2BR



T18-K Shape-K

### Recommended Extras:

Available to purchase separately



B2300 Heat Proof Pad for Tip Changes



FX8803 One-Handed Solder Iron and Solder Feed



FX8804 Hot SMD Tweezers



FX8805 Heavy Duty Soldering Iron



FG100B Tip Thermometer



Solder Wire Holder 611-1 (Single) 611-2 (Double)



FT-710 Solder Tip Polisher



FA-400 Desk Top Fume Extractor



FX-889 Duel Port Soldering Station



FX-888D-SV Silver Variant

