




NOTE:

- 1.OPEN/SHORT/INTERMITTENCE:100%.
- 2.CONDUCTIVE RESISTANCE:2Ω (MAX)
- 3.RoHS & REACH Compliant

Pin OUT

P1	P2
1	1
2	2
3	3

④	MOLDED	45P BLACK PVC		G
③	CONNECTOR	3.5MM PANEL MOUNT FEMALE NICKEL PLATED	1	PCS
②	CONNECTOR	3.5MM NORMAL FEMALE NICKEL PLATED	1	PCS
①	CABLE	(7*0.12BC*2C+SPIRAL 28*0.10BC) PVC OD:4.0	L	MM
NO.	MATERIAL	DESCRIPTION	QTY.	UNIT

Ltemref	Quantity	Title/Name,designation,material,dimension etc			Article No./Reference	
Designed by ALVIN	Checked by HELEN	Approved by - date 10-09-2019	File name	Date 10-09-2019	Scale FREE	
ANGLE:				3.5MM Panel Mount Female/Normal Female 0.3M		
UNIT:MM				Edition 1	Sheet 1/1	