

Fire Door Kit A

a brand of **HOPPE® GROUP**

Corridor Door Locking



APPLICATION

For use on corridor, storage cupboard type doors. Cylinder and turn operates deadbolt. Pull handle and finger plate for door function. Suitable for FD30 and FD60 timber doors.

COMPONENT

CERTIFIRE

Ball Bearing Grade 13 Hinges	1.5pr	CF369
Intumescent pack for hinges	1 pack of 6	CF369
Euro mortice UK deadlock, 76mm, SC	1	CF577
Intumescent pack for deadlock	1	CF577
Overhead door closer, size 2-4, silver	1	CF603
Fire Door Keep Shut sign SS	2	N/A
Finger plate 75x350mm, SS	1	N/A
Pull handle 19x300mm bolt-fix, Grade 304 SS	1 set	N/A
Euro cylinder & turn, 5-pin, 70mm, c/w 3 keys, SC	1	N/A
Euro profile escutcheon Grade 304 SS	1 pr	N/A

TECHNICAL

Max door weight 80kg (60kg Fig6), max door width 1100mm (950mm Fig6)

Deadlock - Grade 2 - Medium frequency use, e.g. internal office doors. Pull handle - Satisfy BS8300:2009.

Door closer - Size 2-4 adjustment by template, separate closing speed and latch action adjustment

BENEFIT

All products from one manufacturer ensures users confidence in compatibility, functionality and after-sales support

UK size sashlock with square faceplate, plus square cornered hinges, provide easier and quicker on-site installation

All products are backed by HOPPE's 5 year guarantee on mechanical operation, subject to T&C's